

# A5B34 Units RTD Input

A5B34 modules plug into a backpanel to provide a single channel of analog input which is filtered, isolated, amplified, linearized, and converted to a proportional DC voltage output signal.

RTD excitation is provided from the module by two matched current sources. When using a three-wire RTD, this method allows an equal current to flow in each RTD lead, which cancels the effects of lead resistances. The excitation currents are very small which minimizes selfheating on the RTD.

Signal filtering is accomplished with a six-pole filter. Two poles of this filter are on the field side of the isolation barrier and the other four are in the output stage. Isolation is provided by transformer coupling, again using a proprietary technique to suppress transmission of common mode spikes or surges.

# Ordering Information

Model	Input	Output
A5B34-01 Pt RTD input	-100 to 100°C	0 to 5V DC
A5B34-02 Pt RTD input	0 to 100°C	0 to 5V DC
A5B34-03 Pt RTD input	0 to 200°C	0 to 5V DC
A5B34-04 Pt RTD input	0 to 600°C	0 to 5V DC
A5B34C-01 Cu RTD input 10 ohms @ 0°C	0 to 120°C	0 to 5V DC
A5B34C-02 Cu RTD input 10 ohms @ 25°C	0 to 120°C	0 to 5V DC
A5B34N-01 Ni RTD input	0 to 300°C	0 to 5V DC

# Performance

#### Input Range

-200 to 850°C (100 ohm Pt)

#### Input Resistance

Normal: 50M ohms Power Off: 40K ohms Overload: 40K ohms

#### Sensor Excitation Current

100 ohm Pt, 120 ohm Ni: 0.25mA

10 ohm Cu: ±1.0mA

#### Input Protection

Continuous: 240V<sub>RMS</sub> max Transient: ANSI/IEEE C37.90.1-1989

#### CMV, Input to Output

Continuous: 1500VRMs max Transient: ANSI/IEEE C37.90.1-1989

#### CMR (50 or 60Hz)

160dB

#### NMR

95dB @ 60Hz, 90dB @ 50Hz

#### Accuracy

A5B34-04: ±0.72°C

### Conformity Error

±0.05% span

#### Stability

Input Offset:  $\pm 0.02^{\circ}\text{C/}^{\circ}\text{C}$  ( $\pm 0.04^{\circ}\text{C/}^{\circ}\text{C}$  max) Output Offset:  $\pm 20\mu\text{V/}^{\circ}\text{C}$  ( $\pm 30\mu\text{V/}^{\circ}\text{C}$  max) Gain:  $\pm 50\text{ppm}$  of reading/ $^{\circ}\text{C}$  max)

#### Nois

Input, 0.1 to 10Hz: 0.2µVrms (0.6µVrms max)
Output, 100KHz: 200µVrms (400µVrms, 800µVP-P max)

Bandwidth, -3dB

4Hz

Response Time, 90% span

200mS

**Output Range** 

0 to +5V

Output Resistance

50 ohms

**Output Protection** 

Continuous short to ground

Output Selection Time, (to ±1mV of Vout)

2.5μS @ 200pF, 3.5μS @ 500pF, 4.0μS @ 1000pF, 6.0μS @ 2000pF

#### **Output Enable Control**

Max Logic "0": +0.8V Min Logic "1": +2.4V Max Logic "1": +36V Input Current, "0, 1": 0.5µA

#### **Power Supply Voltage**

+5V DC ±5%

# Power Supply Current

30mA (33mA max)

#### Power Supply Sensitivity

100 ohm Pt, 120 ohm Ni: 0.05°C/V

10 ohm Cu: 0.5°C/V

#### Environmental

Operating Temperature Range: -40 to +85°C Storage Temperature Range: -40 to +85°C Relative Humidity: 0 to 95% noncondensing RFI Susceptibility: ±0.5% span error @ 400MHz, 5W, 3 ft

#### Approvals (CSA, FM)

Class I; Division 2; Groups A, B, C, D.

#### NOTES

\* Use  $\pm 0.025\Omega$  when using Cu RTDs. R<sub>Z</sub> is the value of the RTD resistance at the lowest point of measurement range. RTI is Referred To Input.



Tel: 248-624-1541 Fax: 248-624-9234 e-mail: sales@acromag.com www.acromag.com

# Rack-Mount I/O Modules



# Ordering Information

# Backpanels and Accessories

#### ■ User's Manual

#### 8500-299

A5B User's Manual. Acromag provides (1) manual with first purchase order at NO CHARGE. Additional manuals must be purchased. The first manual must be specified on the purchase order to ensure delivery.

#### ■ Backpanels

#### APB01

16-channel, non-multiplexed backpanel. Non-addressable analog I/O signal channels provide each module with its own analog bus. The module output switch is continuously "on" when using this backpanel. A temperature sensor is mounted on each channel to provide cold junction compensation for thermocouple modules. Field connections are terminated with four screw terminals at each module site.

#### APR02

16-channel, multiplexed backpanel. Has two analog buses; one for input, one for output. Two-bus configuration takes advantage of the switch-controlled outputs on the input modules and the track-and-hold inputs on the output modules. Up to four APBO2 backpanels can be daisy-chained. Includes temperature sensor and four screw terminals at each module site.

#### APB03

Single channel, non-multiplexed backpanel. See tables below for additional parts required.

#### ΔΡΒΩ/

Dual channel, non-multiplexed backpanel. See tables below for additional parts required.

The following parts are required for DIN rail mounting of one APB03 or APB04 backpanel:

Quantity Part No. Description

1 UM-BEFE35 Base element with snap foot

2 UM-SE Side element

The following parts are required to DIN rail mount two or more APB03 or APB04 backpanels:

Quantity Part No. Description

2 UM-BEFE35 Base element with snap foot

2 UM-SE Side element

Note 1 UM-BE35 Base element w/o snap foot

Note 2 UM-VS Connection pin

Note 1: Quantity = # of panels - 2 Note 2: Quantity = 4 x (# of panels - 2)


#### **■** Cables

#### AXCA004-xx

Interface cable for host system connection. General-purpose 26 conductor ribbon cable for use with APB01/02 backpanels. Specify length, -xx, in feet when ordering.

#### AXCA005

Daisy-chain cable, interconnects up to four APB02 backpanels.



### ■ Power Supplies

#### AXPRT-00

Power supply, 120V AC input (104 to 132V range).

#### AXPRE-003

Power supply, 220V AC input (207 to 265V range).

#### ■ Interface Accessories

#### AXEV

Evaluation board (single channel) with a test socket. See table below for additional parts required.

The following parts are required for DIN rail mounting of one AXEV evaluation board:

Quantity Part No. Description

2 UM-BEFE35 Base element with snap foot

2 UM-SE Side element4 UM-VS Connection pin

#### **AXIF**

Universal interface board. Converts a 26-pin ribbon cable to 26 screw terminals for discrete wire. Mounts on AXRK-002 rack (standoffs, mounting hardware included). Use AXCA004 cable.

#### **AVMEIF**

VMEbus interface board, 32 inputs. Interfaces APB01 backpanel with a 26-pin ribbon cable to Acromag VME A/D boards.

#### **■** Mounting Accessories

#### AXRK-002

19-inch metal rack for mounting the backpanels, power supplies, and universal interface board.

#### UM-BEFE 35

Base element with snap foot (for DIN rail mounting).

#### UM-RF 3<sup>r</sup>

Base element without snap foot (for DIN rail mounting).

#### LINACE

Side element (for DIN rail mounting).

#### UM-VS

Connection pin (for DIN rail mounting).

# ■ Miscellaneous Accessories

#### AXFS-003


Fuses for backpanel, 4 amp, package of 10.

#### AXJP-003

Jumper strap, package of 10 jumpers. Connects I/O modules to direct the output of any input module to the adjacent output module on the APB01 backpanel. The jumpers can also be used to configure I/O addresses on APB02 backpanel.

#### AXR1

Current conversion resistor (precision 20 ohm 0.1%) for A5B32 current input module. Sockets are provided on APB01/02.




AXIF interface board




# Rack-Mount I/O Modules




# **Dimensions**



#### Backpanel APB01, APB02








# **Dimensions**

# 

# Power Supplies AXPRT-003 (115V) and AXPRE-003 (230V)



Dimensions are in inches (millimeters).